




# LED Wide Body Exit Light

## Key Features

- 24m Viewing Distance
- Available with a ceiling or wall mount diffuser
- Long-life 4W LED: 50,000 Hours (AVG)
- 3-Years Manufacturer Warranty on the Complete Fitting
- Compliant with Australian Standards AS2293
- High-Quality Safety Oriented Design

Model: **EX4LED**

[View Online](#)



## Wall Mount



Model: **EX4LED EXWM**  
 Classification: C0/D8,C90/D8  
[View Online](#)

## Ceiling Mount



Model: **EX4LED EXCM**  
 Classification: C0/D20,C90/D20  
[View Online](#)

# Specifications

## General

Body: ABS  
 Rated Voltage: 220-240VAC  
 Operating Temperature: 0~40°C  
 Terminal: PA14

## Illumination

Tube Type: LED  
 Tube AVG Life-Span: 50,000 hours  
 Colour Temperature: 5,000-6000K  
 Beam Angle: 110°C  
 CRI: 80

## Battery

Cell: Ni-MH AA 1,500mAh  
 Charge Time: 16 Hours  
 Discharge Time: 2 Hours  
 Max Temperature: 70°C

Model No.:	Wattage	Flux Output (Lumen)	C0 Classification	C90 Classification	Height (mm)	Width (mm)	Length (mm)
EX4LED EXWM	6.3W	100	D8	D8	160.5	108	380
EX4LED EXCM	6.3W	100	D20	D20	226	160	380

# Spacing Requirements

Classification	Mounting Height (m)															
	2.1	2.4	2.7	3	3.3	3.6	4	4.5	5	6	7	8	9	10	15	20
D8	9.4	9.7	9.9	10.1	10.2	10.3	10.4	10.3	10.2	9.5	8.3	6.1				
D20	13.1	13.6	14.1	14.5	14.8	15.1	15.5	15.8	16.1	16.4	16.3	16.0	15.4	14.5		

# Warranty Information

WBS Technology LED emergency lighting products come with a 3-year manufacturer's warranty. All warranty information and conditions can be found on the WBS website:


[wbstech.com.au/warranty-statement/](http://wbstech.com.au/warranty-statement/)

# Installation Instructions


Please ensure all electrical work is conducted by a licensed electrician:




1. Choose your desired pictogram and install the diffuser
2. Remove the terminal block from the base plate and wire the mains cable as pictured below:



3. Fit the base plate to the wall or ceiling
4. Fix the body to the base plate with the spare screw located inside the fitting and tighten



## Contact Information

 [1300 927 533](tel:1300927533)

 [info@wbstech.com.au](mailto:info@wbstech.com.au)

## Locations

### Silverwater, NSW

Address: [32/2 Slough Ave.,  
Silverwater NSW 2128](#)

Open Hours: 9:00am - 5:00pm  
Monday - Friday

### Mount Waverley, VIC

Address: [66/170 Forster Rd.,  
Mount Waverley VIC 3149](#)

Open Hours: 8:30am - 5:30pm  
Monday - Friday



For more information or to obtain the digital version of this specification, please visit the WBS website:

[wbstech.com.au](http://wbstech.com.au)

